





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20m Ω Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000M Ω Min
Operation Temperature:-40 $^{\circ}$ C to +105 $^{\circ}$ C

Contact Material:Copper Alloy
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 260 $^{\circ}$ C $\pm 5^{\circ}$ C 5S

Ordering Information

PM 254 - * - N - W - * - **

No.of Rows
1=Single Row
2=Dual Row
3=Three Row

No.of Pins
2~40Pin

Type
Z=直插
B=贴片
W=弯脚

Length
(Pitch)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
			X. X	± 0.30	审 核	产品名称	2.54三排 排母 正弯 塑高8.5	版本	A
			X. XX	± 0.20	批 准	TITLE		REV.	
			X. XXX	± 0.10	APPROVAL	产品料号	PM254-3-N-W-8.5-XX(L15.24)	单位	mm
			Angle	$\pm 3.0^{\circ}$	SCALE	PART NO.		页 次	1/1
序号	变更内容	日期			投 影	材料			
No.	MODIFY CONTENT	MODIFY DATE			Projection	MATERIAL			