




RoHS&REACH

REV.	DESCRIPTION	DATE
A	NEW	2025.09.23

- 材料Material:
- 1. 外壳材质: PBT,PA46 (UL 94V-0)
Housing Material: PBT,PA46 (UL 94V-0)
 - 2. 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter
Phosphor Bronze;Gold Plating Over Nickel
- 电气Electrical:
- 1. 额定电压: 125伏
Voltage Rating : 125 V Rms
 - 2. 额定电流: 1.5安培
Current Rating: 1.5 AMP
 - 3. 接触电阻: 最大30毫欧
Contact Resistance: 30 Milliohms MaX
 - 4. 绝缘电阻: 500V下, 绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V
 - 5. 绝缘耐压: 50-60Hz 1000V AC, 1分钟
DIELECTRIC STRENGTH:1000V AC 50Hzor 60Hz, 1MIN.
 - 6. 耐久: 插拔750次以上
Durability: 750 Cycles Min
 - 7. 工作温度: -40℃ ~+85℃
Operation Temperature: -40℃ ~+85℃

5201 - X X X X X X					
Positions	Contacts	Panel	Plastic	Color	Gold Plating
4,6,8	2,4,6,8	0-w/0 Panel 1-w/Panel	1-PBT 2-PA46 3-Other	1-Black 2-Gray 3-Other	1-G/Fu" 2-1u" 3-3u" 4-6u" 5-15u" 6-Other

PC Board Layout
Component Side Shown

DRAWN BY:	FANG	TOLERANCE UNSPECIFIED		SIZE:	1:1	H[®] 恒连电子科技有限公司 EVERCOM ELECTRONIC TECHNOLOGY CO.,LTD				
		X.	±0.5	±2.0"	UNIT:					mm
CHECKED BY:	FANG	.X	±0.38	±1.5"	SIZE:	A4	TITLE: 5201 6P6C 无边			
		.XX	±0.25	±1.0"	REV:	A				
APPROVED BY:	DING	XXX	±0.15	±0.5"	SHEET 1 OF 1	DWG NO:	5201-660XXX		http://www.chinarj45.com	
		PROJECTION		PART NO:		N/A		No:	N/A	