







PC Board Layout
Component Side Shown



1. 外壳材质: PBT,PA46 (UL 94V-0)
Housing Material: PBT,PA46 (UL 94V-0)
2. 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter
Phosphor Bronze;Gold Plating Over Nickel
3. 屏蔽壳: 镀镍铜合金, 厚度0.2mm
Shield: 0.20mm Thickness Copper Alloy
With Nickel Plated

1. 额定电压：125伏
Voltage Rating : 125 V Rms
2. 额定电流：1.5安培
Current Rating: 1.5 AMP
3. 接触电阻：最大30毫欧
Contact Resistance: 30 Milliohms MaX
4. 绝缘电阻：500V下，绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V
5. 绝缘耐压：50-60Hz 1000V AC，1分钟
DIELECTRIC STRENGTH:1000V AC 50Hzor 60Hz， 1MIN.
6. 耐久：插拔750次以上
Durability: 750 Cycles Min
7. 工作温度：-40℃ ～+85℃
Operation Temperature: -40℃ ～+85℃

5203 - X X X X X X X X

Positions	Contacts	Ports	LED Style	Shield	Peg/Tab	Plastic	Color	Gold Plating
8	2,4,6 or 8	1-1x1 2-1x2 3-1x3 4-1x4 5-1x5 6-1x6 7-1x7 8-1x8	0-W/O LED 1-Y/G 2-G/Y 3-R/G 4-G/R 5-Y/Y 6-G/G 7-other	0-W/O Shield 1-W/ Shield	0-W/O Peg 1-FrontPeg 3.05 2-BackPeg 3.85 3-BackPeg 3.05	1-PBT 2-PA46 3-other	1-Black 2-Gray 3-other	1-G/G 2-1u" 3-3u" 4-6u" 5-15u" 6-30u" 7-other

DRAWN BY:	FANG	TOLERANCE UNSPECIFIED		SIZE:	1:1	H[®] 恒连电子科技有限公司 EVERCOM ELECTRONIC TECHNOLOGY CO.,LTD		
		X.	±0.5	±2.0°	UNIT:		mm	
CHECKED BY:	FANG	X.	±0.38	±1.5°	SIZE:		A4	
		XX	±0.25	±1.0°	REV:		A	
APPROVED BY:	DING	XXX	±0.15	±0.5°		TITLE:	5203 1×1 8P8C 屏蔽无弹带灯左黄右绿 脚后3.85	
						DWG NO:	5203-881112XXXX	http://www.chinarj45.com
		PROJECTION			SHEET 1 OF 1	PART NO:	N/A	No: N/A