











RoHS

序号	品名	材质
①	HY2.0直针WTB胶芯	PA66 UL94V-0 米色 白色
②	HY2.0弯针WTB端子	铜合金/表面镀锡



CKT	A	B	CKT	A	B
2	2.0	6.0	12	22.0	26.0
3	4.0	8.0	13	24.0	28.0
4	6.0	10.0	14	26.0	30.0
5	8.0	12.0	15	28.0	32.0
6	10.0	14.0	16	30.0	34.0
7	12.0	16.0	17	32.0	36.0
8	14.0	18.0	18	34.0	38.0
9	16.0	20.0	19	36.0	40.0
10	18.0	22.0	20	38.0	42.0
11	20.0	24.0			

技术指标 (Technical Index):

- 温度范围 (Temperature range): -25° C ~ +85° C.
- 额定电压 (Rated voltage): 200V, AC.
- 额定电流 (Rated current): 2.0A AC, DC.
- 接触电阻 (Contact resistance): ≤ 25mΩ.
- 绝缘电阻 (Insulation resistance): ≥ 1000MΩ.
- 耐压值 (Withstanding voltage): 1000V AC/minute.
- 产品料号 (Product material No.):

A				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1130300216
				X.XXX	±0.10				SHEET	1/1		
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	APPROVE			PROJ.	◆	TITLE:	HY-NAW
		1	2	3	4	5	6	7	8	9		