










RoHS




SECTION A-A



TYPE 1(无K脚)



TYPE 2(打K脚)



CKT	A	B	CKT	A	B
2	2.0	6.0	12	22.0	26.0
3	4.0	8.0	13	24.0	28.0
4	6.0	10.0	14	26.0	30.0
5	8.0	12.0	15	28.0	32.0
6	10.0	14.0	16	30.0	34.0
7	12.0	16.0	17	32.0	36.0
8	14.0	18.0	18	34.0	38.0
9	16.0	20.0	19	36.0	40.0
10	18.0	22.0	20	38.0	42.0
11	20.0	24.0			

技术指标(Technical Index):

- 温度范围(Temperature range): -25° C~+85° C.
- 额定电压(Rated voltage): 200V, AC.
- 额定电流(Rated current): 2.0A AC, DC.
- 接触电阻(Contact resistance): ≤25mΩ .
- 绝缘电阻(Insulation resistance): ≥1000MΩ.
- 耐压值(Withstanding voltage): 1000V AC/minute.
- 产品料号(Product material No.):

深圳市连盛精密连接器有限公司

PART NO.

1130300215

TITLE:

HY-NAW