




材料Material:

1. 外壳材质: PBT,PA46 (UL 94V-0)
Housing Material: PBT,PA46 (UL 94V-0)

2. 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter
Phosphor Bronze;Gold Plating Over Nickel

3. 屏蔽壳: 镀镍铜合金, 厚度0.2mm
Shield: 0.20mm Thickness Copper Alloy
With Nickel Plated

电气Electrical:

1. 额定电压: 125伏
Voltage Rating : 125 V Rms

2. 额定电流: 1.5安培
Current Rating: 1.5 AMP

3. 接触电阻: 最大30毫欧
Contact Resistance: 30 Milliohms MaX

4. 绝缘电阻: 500V下, 绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V

5. 绝缘耐压: 50-60Hz 1000V AC, 1分钟
DIELECTRIC STRENGTH:1000V AC 50Hzor 60Hz, 1MIN.

6. 耐久: 插拔750次以上
Durability: 750 Cycles Min

7. 工作温度: -40℃ ~+85℃
Operation Temperature: -40℃ ~+85℃

56L- X X X X X X X X

Positions	Contacts	Ports	LED TYEP	Shield	Back Peg	Plastic	Gold Plating
6,8	4, 6 or 8	1-1x1 2-1x2 3-1x3 4-1x4 5-1x5 6-1x6 7-1x7 8-1x8	0- W/O LED 1-Y/G 2-G/Y 3-R/G 4-G/R 5-Y/Y 6-G/G 7-Other	0-W/O Shield 1- Shield W EMI 2- Shield W/O EMI 3- W/ half Shield	0-W/O Back Peg 1-1 Back Peg 2-2 Back Peg 3-3 Back Peg	1-PBT 2-PA46 3-Other	1-G/Fu" 2-1u" 3-3u" 4-6u" 5-15u" 6-Other

DRAWN BY:	FANG	TOLERANCE UNSPECIFIED	SIZE:	1:1	H [®] 恒连电子科技有限公司 EVERCOM ELECTRONIC TECHNOLOGY CO.,LTD
CHECKED BY:	FANG	X. ±0.5 ±2.0°	UNIT:	mm	
		.X ±0.38 ±1.5°	SIZE:	A4	
APPROVED BY:	DING	.XX ±0.25 ±1.0°	REV:	A	
		XXX ±0.15 ±0.5°	DWG NO:	56L-882X20XX	
		PROJECTION	SHEET	1 OF 1	PART NO:

56L 1×2 8P8C 屏蔽无弹有灯组合式

http://www.chinarj45.com

No: N/A