




RoHS&REACH

REV.	DESCRIPTION	DATE
A	NEW	2025.09.23

- 材料Material:
1. 外壳材质: PBT,PA46 (UL 94V-0)
Housing Material: PBT,PA46 (UL 94V-0)
 2. 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter
Phosphor Bronze;Gold Plating Over Nickel
 3. 屏蔽壳: 镀镍铜合金, 厚度0.2mm
Shield: 0.20mm Thickness Copper Alloy

- 电气Electrical:
1. 额定电压: 125伏
Voltage Rating : 125 V Rms
 2. 额定电流: 1.5安培
Current Rating: 1.5 AMP
 3. 接触电阻: 最大30毫欧
Contact Resistance: 30 Milliohms MaX
 4. 绝缘电阻: 500V下, 绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V
 5. 绝缘耐压: 50-60Hz 1000V AC, 1分钟
DIELECTRIC STRENGTH:1000V AC 50Hzor 60Hz, 1MIN.
 6. 耐久: 插拔750次以上
Durability: 750 Cycles Min
 7. 工作温度: -40℃ ~+85℃
Operation Temperature: -40℃ ~+85℃

5905 - X X X X X X X X X

Positions	Contacts	Ports	Led	Shield	Peg/Tab	Back Peg	Plastic	Gold Plating
10/8	2/4/6/8	1-1×1 2-1×2 3-1×3 4-1×4 5-1×5 6-1×6 7-1×7 8-1×8	0-w/O Led 1-Y/G 2-G/Y 3-R/G 4-G/R 5-Y/Y 6-G/G 7-Other	0-w/O Shield 1-Shielded w/O EMI 2-Shielded w EMI	0-w/O Back Peg 1-Front Peg 4.57 2-Front Peg 3.68 3-Back Peg 3.05	0-w/O Back Peg 1-1 Back Peg 2-2 Back Peg 3-3 Back Peg	1-PBT 2-PA46 3-Other	1-G/Fu" 2-1u" 3-3u" 4-6u" 5-15u" 6-Other

DRAWN BY: FANG	TOLERANCE UNSPECIFIED	SIZE: 1:1	H[®] 恒连电子科技有限公司 EVERCOM ELECTRONIC TECHNOLOGY CO.,LTD
CHECKED BY: FANG	X. ±0.5 ±2.0°	UNIT: mm	
APPROVED BY: DING	.X ±0.38 ±1.5°	SIZE: A4	
	.XX ±0.25 ±1.0°	REV: A	
	XXX ±0.15 ±0.5°	PROJECTION	
		SHEET 1 OF 1	
TITLE: 5905 1×1 8P8C 屏蔽无弹脚后3.05 左黄右绿			
DWG NO: 5905-8811130XX			http://www.chinarj45.com
PART NO: N/A			No: N/A