





RoHS&REACH

REV.	DESCRIPTION	DATE
A	NEW	2025.09.23

- MATERIAL:
- 1.HOUSING MATERIAL: ABS
 - 2.CONTACT MATERIAL: ROUND PINS-0.46mm DIAMETER PHOSPHOR BRONZE;GOLD PLATING OVER NICKEL,30U
 - 3.WIRE:UL 1061 26#

- ELECTRICAL
- 1.VOLTAGE RATING : 125 VAC RMS
 - 2.CURRENT RATING: 1.5 AMP
 - 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX
 - 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @500V DC
 - 5.DIELECTRIC WITHSTANDING RESISTANCE: 1000V AC RMS 60Hz.1MIN
 - 6.DURABILITY: 750 CYCLES MIN
 - 7.TEMPERATURE: -40°C/+85°C
 - 8.CRIMPING STRENGTH:2.3KG MIN



4	反端	4	黄铜	
3	金线	4	FU	
2	电子线	4	UL 1061 26AWG	扭线沾锡
1	塑壳	1	ABS	灰色
序号	物料名称	数量	材质	备注

4	黑	300mm	5.0mm
3	红	300mm	5.0mm
2	绿	300mm	5.0mm
1	黄	300mm	5.0mm
线序	颜色	长度	剥头

DRAWN BY: FANG

CHECKED BY: FANG

APPROVED BY: DING

TOLERANCE UNSPECIFIED

X. ±0.5 ±2.0°

.X ±0.38 ±1.5°

.XX ±0.25 ±1.0°

XXX ±0.15 ±0.5°

PROJECTION

SIZE: 1:1

UNIT: mm

SIZE: A4

REV: A

SHEET 1 OF 1

H[®]

恒连电子科技有限公司

EVERCOM ELECTRONIC TECHNOLOGY CO.,LTD

TITLE: 616M 4P4C ABS灰色 L=300(黄绿红黑) FU

DWG NO: 616M-44221 L=300

PART NO: N/A

http://www.chinarj45.com

No: N/A