




RoHS



技术指标 (Technical Index):



- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
- 不同pin位吸盖加入/取出力有差异, 实属正常现象。
(It is normal than there are difference between suction cap and suction cap at different Pin positions)
- 温度范围 (Temperature range): $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 额定电压 (Rated voltage): 200V, AC.
- 接触电阻 (Contact resistance):
 $\leq 55\text{m}\Omega$ (initial) per contact, $\leq 25\text{m}\Omega$ Change allowed.
- 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.
- 产品料号 (Product material No.):

WT200FL		***	*	*	***	00	胶芯有LOGO:WD (Housing with LOGO:WD)
NO OF CKT (产品PIN数)						0W	胶芯无LOGO (Housing without LOGO)
Plating (电镀方式)							
0: 端子全雾锡 (Terminal all mist tin)							
1: 端子全金 (Terminal G/F OVER ALL)							
4: 端子全亮锡 (Terminal all bright tin)							
Packing (包装方式)							
T: TUBE 管装							
R: TAPE & REEL 卷装							
C: TAPE & REEL WITH COVER 加吸盖卷装							



WITH COVER

CKT	DIM A	DIM B	DIM C
2	2.00	4.80	7.95
3	4.00	6.80	9.95
4	6.00	8.80	11.95
5	8.00	10.80	13.95
6	10.00	12.80	15.95
7	12.00	14.80	17.95
8	14.00	16.80	19.95
9	16.00	18.80	21.95
10	18.00	20.80	23.95
11	20.00	22.80	25.95
12	22.00	24.80	27.95
13	24.00	26.80	29.95
14	26.00	28.80	31.95
15	28.00	30.80	33.95
16	30.00	32.80	35.95
17	32.00	34.80	37.95
18	34.00	36.80	39.95
19	36.00	38.80	41.95
20	38.00	40.80	43.95



OPERATION

DRAW

CHECK

APPROVE

SCALE

FIT

UNIT

SIZE

SHEET

PROJ.

mm

A4

1/1

深圳市连盛精密连接器有限公司

PART NO.

1130300189

TITLE:

PH-NAWV

REV DATE MODIFICATION DESCRIPTION

CHANGE

DIM TOL

1

2

3

4

5

6

7

8

9