

[illegible]

RoHS

G

F

E

D

C

B

A

N-0.5±0.03(SQ)

2.00±0.15(PITCH)

①

DIMA±0.2

DIMB±0.15

DIMC±0.25

2.65±0.2

②

③

①

②

③

6.0

1.6

2.3

5.6

0.12

PCB LAYOUT

DIMA±0.1

2±0.05

1.9±0.1

3.8Min.

4.00

1.4Min.

2.3

1.2±0.1

0.50

CONN.

技术指标:

1.工作温度：-25° C~ 105° C.

2.额定电压：200V DC/AC(rms).

3.额定电流：2.0A.

4.接触电阻：≤20mΩ.

5.耐压值：500V AC/minute.

6.绝缘电阻：≥1000MΩ.

7.产品料号：

CTK

DIM A

DIM B

DIM C

2

2.00

4.80

7.95

3

4.00

6.80

9.95

4

6.00

8.80

11.95

5

8.00

10.80

13.95

6

10.00

12.80

15.95

7

12.00

14.80

17.95

8

14.00

16.80

19.95

9

16.00

18.80

21.95

10

18.00

20.80

23.95

11

20.00

22.80

25.95

12

22.00

24.80

27.95

13

24.00

26.80

29.95

14

26.00

28.80

31.95

15

28.00

30.80

33.95

16

30.00

32.80

35.95

17

32.00

34.80

37.95

18

34.00

36.80

39.95

19

36.00

38.80

41.95

20

38.00

40.80

43.95

深圳市连盛精密连接器有限公司

PART NO.

TITLE:

1130300198

PH-AWR

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

OPERATION

X.X

X.XX

X.XXX

Angle

DIM

±0.30

±0.20

±0.10

±3°

TOL

DRAW

CHECK

APPROVE

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆◀▶

1

2

3

4

5

6

7

8

9

[illegible][illegible][illegible]