

Specifications

备注(Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing:PA9T+30%G.F UL94V-0, Color:Black

端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact: Bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current:2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance:20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperature Range: -40°C to $+105^{\circ}\text{C}$



Ordering Information

F243-11 05 A0 C SU C 1

NQ OF PINS	CONTACT PLATING	INSULATOR	PACKING
PER ROW	Full of Gold	Semigold	MATERIAL:
1-40P	A0=0.8u"	B0=0.8U"	A: PE Bag
	A1=1u"	B1=1U"	B: Tape & Reel
	A2=1.5u"	B2=1.5U"	C: Tube
	A3=2u"	B3=2U"	D: Tube+CAP
	A4=3u"	B4=3U"	E: Tray
	A5=5u"	B5=5U"	
	A6=10u"	B6=10U"	
	A7=15u"	B7=15U"	
	A8=20u"	B8=20U"	
	A9=30u"	B9=30U"	
	S1=Ordnary Tin Plated		
	S2=Matte Tin Plated		
	S3=Tin plated High temperature		

RoHS
COMPLIANT

客编: K1349

注意事项

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM	www.yxcon.com		
				X.XX	±0.20	SIZE		A4	DESIGN	李官淼2021.10.11	PART NO
				X.XXX	±0.10	SHEET		1/1	CHECK		TITLE
				Angle	±3°	PROJ.			APPROVE		Customer No.
A0	2021.10.11	/	新版发行								F243-1105A0CSUC1 2.0排母4.3mm塑高 1*5P 180度 DIP:2.8mm U型 PA9T料 镀黄金 管装 K1349
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION								