

备注 (Remark)

1. 材料 (MATERIAL)





胶芯: PA6T+30%G. F UL94V-0, 颜色: 黑色.
Housing: PA6T+30%G. F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金
Contact: Brass, GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

额定电流: 2 AMP
 Rating Current: 2 AMP.
 接触阻抗: 20 mΩ MAX.
 Contact Resistance: 20 mΩ MAX.
 绝缘阻抗: 1000 MΩ MIN.
 Insulating Resistance: 1000 MΩ MIN.
 耐电压: AC 500V/分钟.
 Withstanding Voltage: AC 500V/Minute.
 温度范围: -40° C to +105° C
 Temperature Range: -40° C to +105° C

P220-12 05 A0 B S 082 A 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Pin at ing	INSULATOR MATERIAL:	LENGTH OF TERM NAL	PACKING
10: 1.0mm	2~40P	Full G Gold	B0=0.8U'	B PA6T	A: PE Bag
15: 1.5mm		A1=1u"	B1=1U'	C PA9T	B: Tape & Reel
20: 2.0mm		A2=1.5u"	B2=1.5U'	D LCP	C Tube
		A3=2u"	B3=2U'		D Tube+CAP
		A4=3u"	B4=3U'		E: Tray
		A5=5u"	B5=5U'		
		A6=10u"	B6=10U'		
		A7=15u"	B7=15U'		
		A8=20u"	B8=20U'		
		A9=30u"	B9=30U'		
		S1=Ordinary Tin Plated			
		S2=Matte Tin Plated			
		S3=Tin-plated High-temperature			



RoHS
COMPLIANT

客编: K1031

注意事项

1. 带*为品质重点检验尺寸
2. DIP端不能有毛边

				OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.25	UNIT		MM					
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2021.04.02	PART NO	P220-1205A0BS082A1		
				X.XXX	±0.10								
A0	2021.04.02	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE:	2.0排针 2*5P L=8.2/2.3 180度 DIP端不能有毛边		
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	Dim.	TOL	PROJ		APPROVE		Customer No	PA6T 镀普金 1000个/袋		