

Ordering Information
B256-1 XX XX X S X X 9

1. 材料(MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.

Housing:PA6T+30%G. F UL94V-0, Color:Black

四方针：黄铜，镍底30u"MIN, 表面镀金0.8u"MIN

Contact:Brass, 0. 8u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current:2 AMP.

接觸阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.



Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V.

Withstanding Voltage:AC 500V.


温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40° C to+105° C



NQ OF PINS	Contact	Plating	INSULATOR	B-BACK	PACKING
4-100P	Full Contact Gold	Semi-gold	MATERIAL:	G Grey427	A: PE Bag
	A0=0.8u"	B0=0.8U'	B: PA6T	E: Grey413	B: Tape & Reel
	A1=1u"	B1=1U'	C: PA9T	WWhite	C: Tube
	A2=1.5u"	B2=1.5U'	D: LCP	U: Blue	D: Tube+CAP
	A3=2u"	B3=2U'			E: Tray
	A4=3u"	B4=3U'			
	A5=5u"	B5=5U'			
	A6=10u"	B6=10U'			
	A7=15u"	B7=15U'			
	A8=20u"	B8=20U'			
	A9=30u"	B9=30U'			
	S1=Ordinary	Tin Plated			
	S2=Matte	Tin Plated			
	S3=Tin-plated	High-temperature			

注：同系列成品共用此图纸



注意事项

1. 带*为品管检验尺寸。

						OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
						X.X	+0.25	UNIT		MM				
						X.XX	+0.20	SIZE	A4	DESIGN	周芳杰	PART NO	B256-1XXXXXX9	
						X.XXX	+0.10							
A0	2020.03.04	新版发行	周芳杰	刘贵宝		Angle	+13°	SHEET	1/1	CHECK		TITLE	BH2.0*5.6 XXP 180度 L=8.2*2.8 端头带窗口	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE		DIM	TOL	PROJ.		APPROVE		Customer No.		