

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色:黑色.

Housing:PA6T+30%G.F UL94V-0, Color:Black

端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact:Bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current:2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance:20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40° C to+105° C

Temperture Range: -40° C to+105° C



Ordering Information

F243-12 08 A0 B SU C 2

NO. OF PINS
PER ROW
2-40P

Full Cl Gbl d

Semi-gol d

INSULATOR MATERIAL:

PACKING

A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"
S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Ti-n-plated High-temperature

B0=0.8U"
B1=1U"
B2=1.5U"
B3=2U"
B4=3U"
B5=5U"
B6=10U"
B7=15U"
B8=20U"
B9=30U"

A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

RoHS
COMPLIANT

注意
事项

1. 带*为品质重点
检验尺寸

Yxcon

东莞市宇熙精密连接器有限公司

www.yxcon.com

Dongguan Yuxi Electronic Co.,Ltd.

OPERATION

SCALE

Fit

X X ±0.25

UNIT

MM

X XX ±0.20

X XXX ±0.10

Angle ±3°

Dim Tol

PROJ.

1/1

CHECK

APPROVE

DESIGN

李官森2022.06.02

SHEET

APPROVE

PART NO

TI TLE:

2.0排母4.3mm塑高 2*8P 180度 DIP:2.7mm

U型 塑宽=4.0 PA6T料 镀普金

Customer No.

F243-1208A0BSUC2

2.0排母4.3mm塑高 2*8P 180度 DIP:2.7mm

U型 塑宽=4.0 PA6T料 镀普金

Customer No.

新版发行

MODIFICATION DESCRIPTION

REV

DATE

SYMBOL