





Ordering Information
P125-22 08 A0 B S 210 A 1

30u" MIN NICKEL UNDERPLATING OVER ALL

Temperture Range: -40 ° C to+105° C



HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL:	LENGTH OF TERM NAL	PACKING A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
15: 1.5mm	2-40P	Full Cr Gold	BO=0, 8U	A: PBT	
17: 1.7mm		A1=1u"	B1=1U	B: PA6T	C: Tube
20: 2.0mm		A2=1.5u"	B2=1, 5U	C: PA6T	D: Tube+CAP
25: 2.54mm		A3=2u"	B3=2U	D: LCP	E: Tray
30: 3.0mm		A4=3u"	B4=3U		
		A5=5u"	B5=5U		
		A6=10u"	B6=10U		
		A7=15u"	B7=15U		
		A8=20u"	B8=20U		
		A9=30u"	B9=30U		
		S1=Ordinary Tin Plated			
		S2= Matte Tin Plated			
		S3= Tin-plated High-temperature			

客编: K6012

注意事项

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2021.07.09	PART NO	P125-2208A0BS210A1	
				X.XXX	±0.10							
A0	2021.07.09	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE	2.54排针 2*8P*2 L=21.0/3.0/6.0 180度 PA6T 镀黄金 200/袋	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.		

Yxcon 东莞市宇熙精密连接器有限公司
www.yxcon.com Dongguan Yuxi Electronic Co., Ltd.