


Rating :

10A 250V AC KC CE TUV 3C

Insert And Extract Force: 1.36kgf~6.8kgf

Operating Life: ≥5000 cycles

Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min
terminals to Base:2500V AC (50-60Hz)1min

Leakage Current : 1mA

Insulation Resistance: ≥100MΩ 500V DC

A4				普通公差									
A3				COMMON TOLERANCE :									
A2				UP TO 5	±0.20	单 位	mm	投 影		品 名	Ac Inlet	比 例	Free
A1				ABOVE 5 TO 30	±0.30	UNIT		核 对		PRODUCT NAME			
				ABOVE 30	±0.50	DRAWN BY	吴 瑜	CHECKED BY		型 号	LZ-14		
				ANGULAR	±5°	日 期	2020. 10. 16	核 准		图 号	LZ-14-T2		
REV.	DATE	REVISION	DESCRIPTION	ISSUE		DATE		APPROVAL BY		DWG NO.			