

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA6T无卤+30%G. F UL94V-0, 颜色: 黑色.

Housing: PA6T无卤+30%G. F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C




Ordering Information

P220-21 09 A0 C S 140 A 2

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL	LENGTH	PACKING
10: 1.0mm 15: 1.5mm 20: 2.0mm	1~40P	Full of Gold A0=0.8u" A1=1u" A2=1.5u" A3=2u" A4=3u" A5=5u" A6=10u" A7=15u" A8=20u" A9=30u"	Semi-gold B0=0.8u" B1=1u" B2=1.5u" B3=2u" B4=3u" B5=5u" B6=10u" B7=15u" B8=20u" B9=30u"	TERMINAL	A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature



RoHS
COMPLIANT

HF

客编: K7200

注意事项

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.25	UNIT		MM					
				X.XX	±0.20								
				X.XXX	±0.10	SIZE		A4	DESIGN	李官森2021.09.25		PART NO	P220-2109A0CS140A2
A0	2021.09.25	/	新版发行	Angle	±3°	SHEET		1/1	CHECK			TITLE	2.0排针 1*9P*2 L=14.0/2.6/2.6 180度 总长18±0.3 (使用0.15刀片切) PA6T无卤料 镀普金 1K/袋 K7200
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.			APPROVE			Customer No.	