

10

10

10

1. 材料 (MATERIAL)

Housing: PA9T+30%G. F UL94V-0, Color: Black

Housing:PA9T+30%G.F UL94V-0,Color:Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金
Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current: 2 AMP.

接触阻抗: 20 m Ω MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 M Ω MIN.




Insulating Resistance: 1000 M Ω MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperature Range: -40°C to $+105^{\circ}\text{C}$



COMPLIANT

客编: K1031

注
1. 带*为品质重点检验尺寸

意 事 项

				 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co., Ltd.					
			OPERATION	SCALE		FIT			
			X.X	UNT		MM	WWW.YXCON.COM		
			X.XX	±0.20		A4	DESIGN	刘伟 2021.08.07	PART NO
			X.XXX	±0.10		1/1	CHECK	TITLE:	P220-2203A0CS170A2
A0	2021.08.07	/	Angle	±3°		SHEET	PROJ.	Customer No.	Pt2.0 2x3x2 L=17.0/2.5/4.0 180度 DIP座不能 有毛边 PVA材料 普金 1000PCS/袋
REV	DATE	SMBO	MOUNTING DESIGN PIN	DIM	TOL	APPROVE			