

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色:黑色.

Housing:PA9T+30%G.F UL94V-0, Color:Black

端子: 青铜, 镍底30u"MIN, 表面镀金1u"

Contact:Bronze, 1u" GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance:20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V.

Withstanding Voltage:AC 500V.

温度范围: -40° C to+105° C

Temperture Range: -40° C to+105° C



Ordering Information

F185-12 03 A0 C RY E 2

NO. OF PINS
PER ROW
2-40P

Contact
Full of Gold

Plating
Semi-gold

INSULATOR
MATERIAL:

PACKING
A: PE Bag

A0=0.8u"

B0=0.8U"

A: PBT

B: Tape & Reel

A1=1u"

B1=1U"

B: PA6T

C: Tube

A2=1.5u"

B2=1.5U"

C: PA9T

D: Tube+CAP

A3=2u"

B3=2U"

D: LCP

E: Tray

A4=3u"

B4=3U"

A5=5u"

B5=5U"

A6=10u"

B6=10U"

A7=15u"

B7=15U"

A8=20u"

B8=20U"

A9=30u"

B9=30U"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

客编:K5005

注意事项

1. 注意产品总高, 控制在公差范围内,
2. 端子切脚使用,
3. 带*为品管检验尺寸。

				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	+0.25	UNIT		MM				
				X.XX	+0.20	SIZE	A4	DESIGN	杨哲	PART NO	F185-1203A0CRYE2	
				X.XXX	+0.10							
A0	2019/12/19	新版发行		杨哲	方总	Angle	+13°	SHEET	1/1	CHECK	TITLE	FH2.54*8.5 2*3P 90度 切脚 内径1.0 DIP:2.4 PA9T料 普金 500PCS/盘 K5005
REV	DATE	MODIFICATION DESCRIPTION			CHANGE	APPROVE	DIM	TOL	PROJ.		APPROVE	