

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀金足0.8u"

Contact: Brass, 0.8u" MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 1 AMP

Rating Current: 1 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C


Temperture Range: -40° C to +105° C



Ordering Information

P315-22 07 A0 C S 155 B 2

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full of Gold	Plating Semi-gold	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
08: 0.8mm 10: 1.0mm 15: 1.5mm	2-50P	A0=0.8u" A1=1u" A2=1.5u" A3=2u" A4=3u" A5=5u" A6=10u" A7=15u" A8=20u" A9=30u"	B0=0.8u" B1=1u" B2=1.5u" B3=2u" B4=3u" B5=5u" B6=10u" B7=15u" B8=20u" B9=30u"	B: PA6T C: PA9T D: LCP		A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
S1=Ordinary Tin Plated S2=Matte Tin Plated S3=Tin-plated High-temperature						




不允许有毛边

RoHS
COMPLIANT

客编: V1195

注意事项

- 带*为品质重点检验尺寸.
- 外观毛边小于0.1mm, 且对插面不能有毛边.

				OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.40	UNIT		MM					
				X.XX	±0.25	SIZE	A4	DESIGN	李官森2022.04.21	PART NO	P315-2207A0CS155B2		
				X.XXX	±0.15								
A0	2022.04.21	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE:	PH1.27*1.5 2*7P*2 L=15.5/1.8/1.9 180度 与客户外观一致 毛边0.1以下/PA9T/金足0.8U" (CAP-LCP料) +150/黑色卷 V1195		
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Cust order No.			