

Specifications

Ordering Information

F136-12 05 A2 B MU B 2

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G.F UL94V-0, Color: Black

端子: 青铜, 镍底30u"MIN, 表面镀金1.5u"MIN

Contact: Bronze, 1.5u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C

NO. OF PINS
PER ROW
2~40P




Contact Plating
Full of Gold
A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"

Semi-gold
B0=0.8u"
B1=1u"
B2=1.5u"
B3=2u"
B4=3u"
B5=5u"
B6=10u"
B7=15u"
B8=20u"
B9=30u"

INSULATOR
MATERIAL:
B: PA6T
C: PA6T
D: LCP

PACKING
A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

S1=Grinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature




RoHS
COMPLIANT

客编: K9938

注意事项

1. 带*为品质重点检验尺寸



OPERATION

SCALE

Fit

Yxcon
www.yxcon.com

东莞市宇熙精密连接器有限公司
Dongguan Yuxi Electronic Co., Ltd.

X.X ±0.25

UNIT

MM

X.XX ±0.20

SIZE

A4

DESIGN

李官森2022.04.22

PART NO

F136-1205A2BMUB2

X.XXX ±0.10

SHEET

1/1

CHECK

TITLE

PH2.54*3.6 2*5P SMT:7.2 总长12.7 (GRS)

Angle ±3°

PROJ.

APPROVE

Cust order No.

U型 带柱 镀金1.5U 青铜 PA6T CAP+卷装/800PCS

DI M TOL

A0 2022.04.22 / 新版发行

REV DATE SYMBOL MODIFICATION DESCRIPTION