






PRODUCT NO.	1
DSHP04TSGE1	RoHS compliant



(Construction)



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	1u"~3u" Gold
④	Terminal	Brass	1u"~2u" Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	1u"~3u" Gold
⑦	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED				INSPECTION COPY	
LINER				PROJECTION	
0 ± 0.25				0. ± 2°	
.00 ± 0.15				.0 ± 1°	
.000± 0.10				.00± 0.5°	
DESIGN				03/20/12	
DRAWING					
CHECK					
APPRO.					
FILE NO. DSHPO4TSGE1-A				SIZE UNIT SCALE SHEET REV.	
A4 mm				2 : 1 10F-1 A	

NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations


2. PLATING:

GOLD FLASH 1u"~2u" SOLDER TAIL,
1u"~3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX I S G E I

- 【包装方式: T=管装 R=Reel】
- 【电镀层: E=接触部 1u"~3u" 焊脚部1u"~2u"】
- 【G=镀金 S=内镀金(接触部)外镀锡(焊脚部)】
- 【脚型: S脚 / J脚 / H脚 / A脚 / Z脚】
- 【T=低推贴胶 S=低推不贴胶 L=长推】
- 【产品P数: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P】



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)