

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

P125-22 03 A0 C S 230 A 3

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
15: 1.5mm	2~40P	Full of Gold	A: PBT	A: PE Bag	A: PE Bag
17: 1.7mm		Semi-gold	B: PA6T	B: Tube	B: Tape & Reel
20: 2.0mm		A0=0.8u"	C: PA9T	C: Tube	C: Tube
25: 2.54mm		A1=1u"	D: LCP	D: LCP	D: Tube+CAP
30: 3.0mm		A2=1.5u"			E: Tray
		A3=2u"			
		A4=3u"			
		A5=5u"			
		A6=10u"			
		A7=15u"			
		A8=20u"			
		A9=30u"			
		S1=Ordinary Tin Plated			
		S2=Matte Tin Plated			
		S3=Tin-plated High-temperature			

RoHS
COMPLIANT

客编: K5005

注意事项

1. 带*为品质重点检验尺寸

OPERATION

SCALE

Fit

Yxcon

东莞市宇熙精密连接器有限公司

X.X ±0.25

UNIT

MM

www.yxcon.com

Dongguan Yuxi Electronic Co., Ltd.

X.XX ±0.20

SIZE

A4

DESIGN

李官森2022.01.06

PART NO

P125-2203A0CS230A3

X.XXX ±0.10

SHEET

1/1

CHECK

TITLE

2.54排针 2*3P*2 L=23.0/6.5/6.5

180度 PA9T 镀普金 袋装 K5005

Angle ±3°

PROJ.

APPROVE

Customer No.

DIM TOL

A0 2022.01.06 /

新版发行

REV DATE SYMBOL

MODIFICATION DESCRIPTION