

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

端子: 磷铜, 镍底30u"MIN, 表面镀半金高温雾锡10u"MIN

Contact: Phosphor, 10u"MIN Half gold Matte Tin Plated high temperature
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Rating Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V.

Withstanding Voltage: AC 500V.

温度范围: -40° C to +105° C

Temperature Range: -40° C to +105° C

Ordering Information

F244-12 07 C6 C MU B 2




NO. OF PINS
PER ROW
2-40P

Contact Plating
Full of Gold
A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"

INSULATOR
MATERIAL:
A: PBT
B: PA9T
C: PA9T
D: LCP

PACKING
A: PE Bag
B: Tape & Peel
C: Tube
D: Tube+CAP
E: Tray

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High temperature
C6=10u"MIN Half gold Matte Tin Plated high temperature



						OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.			
						X.X	+0.25	UNIT		MM					
						X.XX	+0.20	SIZE	A4	DESIGN	杨哲	PART NO	F244-1207C6CMUB2		
						X.XXX	+0.10								
						Angle	+13°	SHEET	1/1	CHECK		TITLE:	FH2.0*4.4 2*7P SMT:6.2 倒接式/磷铜/PA9T料 塑宽=4.0/半金10U"高温雾锡/CAP+卷装		
REV	DATE	MODIFICATION DESCRIPTION			CHANGE	APPROVE	DIM	TOL	PROJ.		APPROVE		Customer No.		