





Specifications

备注 (Remark)
1. 材料 (MATERIAL)
胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.
Housing: PA9T+30%G.F UL94V-0, Color: Black
端子: 青铜, 镍底30u"MIN, 表面镀金足1u"
Contact: Bronze, 1u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL
2. 特性 (characteristics):
额定电流: 3 AMP
Rating Current: 3 AMP.
接触电阻: 20 mΩ MAX.
Contact Resistance: 20 mΩ MAX.
绝缘电阻: 1000 MΩ MIN.
Insulating Resistance: 1000 MΩ MIN.
耐电压: AC 500V/分钟.
Withstanding Voltage: AC 500V/Minute.
温度范围: -40° C to +105° C
Temperature Range: -40° C to +105° C



Ordering Information

F185-11 07 A1 C MU B 1

NO. OF PINS	CONTACT PLATING	INSULATOR	PACKING
PER ROW	Full or Gold	Semi-gold	Anti-static
2-40P			
	Full or Gold	Semi-gold	Anti-static
	A0=0.8u"	B0=0.8u"	A: PET Bag
	A1=1u"	B1=1u"	B: Tape & Reel
	A2=1.5u"	B2=1.5u"	C: Tube
	A3=2u"	B3=2u"	D: Tube+Cap
	A4=3u"	B4=3u"	E: Tray
	A5=5u"	B5=5u"	
	A6=10u"	B6=10u"	
	A7=15u"	B7=15u"	
	A8=20u"	B8=20u"	
	A9=30u"	B9=30u"	
	S1=Optional Tin Plated	S2=Optional Tin Plated	
	S3=Optional High Temperature		

RoHS COMPLIANT
客编: K6063
1. 带*为品质重点检验尺寸
注意事项

OPERATION	SCALE	UNIT	Fit	MM	DESIGN	DATE	PART NO.	TI TLE	Customer No.
XX	±0.25					2022.05.17	F185-1107A1CMB1	2.54排母8.5mm间距 1*7P SMT:4.5 U型 青铜 PA9T料 镀金足1u" CAP:350PCS/卷装 K6063	
XX	±0.20								
XXX	±0.10								
Angle	±3°								
DM	TOL								
DATE	SMBQ								
REV									

YXCON 东莞市宇熙精密连接器有限公司
Dongguan Yuxi Electronic Co.,Ltd.