

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u", 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

P115-11 01 A0 C S 085 A 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
15: 1.5mm	1~40P	Full of Gold	A: PBT	A: PE Bag	B: Tape & Reel
17: 1.7mm		A0=0.8u"	B: PA6T	C: PA9T	C: Tube
20: 2.0mm		A1=1u"	C: LCP	D: LCP	D: Tube+CAP
25: 2.54mm		A2=1.5u"			E: Tray
		A3=2u"			
		A4=3u"			
		A5=5u"			
		A6=10u"			
		A7=15u"			
		A8=20u"			
		A9=30u"			
		S1=Ordinary Tin Plated			
		S2=Matte Tin Plated			
		S3=Tin-plated High-temperature			
		C1=1u" MIN GOLD PLATED WITH HIGH TEMPERATURE MATTE TIN			

Recommended P.C.B LAYOUT

General Tolerance ± 0.05

RoHS
COMPLIANT

客编: K2222

注意事项

- 带序号为必检尺寸, 带*为重点检验尺寸
- 保持力0.8kg Min (公司标准)

				OPERATION		SCALE		Fit		东莞市宇熙精密连接器有限公司			
				X.X	± 0.30	UNIT		MM		www.yxcon.com Dongguan Yuxi Electronic Co., Ltd.			
				X.XX	± 0.20	SIZE	A4	DESIGN		陈丽明2025/5/26 PART NO. P115-1101A0CS085A1			
				X.XXX	± 0.10	SHEET		1/1	CHECK	PH2.54*1.5 1*1P L=8.5/3.0 180度			
				Angle	$\pm 3^\circ$					PA9T金发料 镀普金 袋装 K2222			
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DI M	TOL	PROJ.		APPROVE		Cust oner No.			
A0	2025/5/26	/	新版发行										