



本公司智慧財產，未經同意不得複製
DAILYWELL copyright, may not be used
without permission from DAILYWELL



Model No.	POS.1	POS.2
		
PAS6	OFF	(ON)
Term. Comm.	OPEN	1-3
SCHEMATIC		

SWITCH FUNCTION

	PART NO.	PART NAME	Q'TY
1	MNU- PA03	M12x0.75 NUT	1
2	MNU-1M09	LOCKING WASHER	1
3	FSU- PA01	EVA WASHER	1

FILE NAME:HARDWARE-0011

SPECIFICATIONS

Max. current/voltage rating with resistive load:

400 mA 32 VAC - 100 mA 50 VDC - 125 mA 125 VAC.

INITIAL CONTACT RESISTANCE: 50 mΩ max.

INSULATION RESISTANCE: 1 GΩ min. at 500 VDC.

DIELECTRIC STRENGTH: 1,000 VAC rms.

ELECTRICAL LIFE AT FULL LOAD: 500,000 cycles.

PANEL THICKNESS: 1.5 mm (.059 inch) min. ~ 4 mm (.157 inch) max.

TOTAL TRAVEL: 1.5 mm(.059 inch).

OPERATING FORCE: 2N~5N.

CONTACT BOUNCE: 10 ms.

MECHANICAL LIFE: 1,000,000 cycles.

TORQUE: 0.5 Nm max. applied to nut.

SOLDERING: 350°C max. for 5 seconds.

DEGREE OF PROTECTION: IP67

MATERIALS

CASE: Diallyl phthalate (DAP)(UL 94V-0).

CAP: Polyamide 6/6.

BUSHING: Polyamide 6/6.

TERMINALS: Copper, Gold over silver plated.

CONTACT: Brass, Gold over silver plated.

RoHS & Lead Free

[illegible]

DAILYWELL

德利威電子股份有限公司

版本 : D

表單編號：QR-0507