






REV.	ECN NO OR DESCRIPTION	REVISED	DATE



SPECIFICATION NOTES:
ELECTRICAL:
1.VOLTAGE RATING: 125 VAC RMS
2.CURRENT RATING: 1.5 AMP
3.CONTACT RESISTANCE: 20m MAX.
4.INSULATION RESISTANCE: 1000M MIN. AT500V DC.
5.DIELECTRIC STRENGTH: 1000 V AC OR
1500V DC RMS AT 0.5mA 50 Hz / 60 Hz FOR 1MINUTE

MECHANICAL:
1.HOUSING:LCP BLACK, UL 94V-0
2.CONTACT:PHOSPHOR BRONZE T=0.30MM
3.PLATING:GOLD PLATING AT CONTACT AREA, MATTE
TIN AT TAIL 100U MIN., NICKEL 30U MIN. OVER ALL.
4.SHELL:BRASS T=0.20
5.OPERATING LIFE:750 CYCLES MIN.
6.MATING/UNMATING FORCE: 30N/3.06KGf MAX.
7.RETENTION STRENGTH:50N OR 30N MIN.FOR 60S±5S

ENVIRONMENTAL:
1.STORAGE:-40°C TO +85°C RELATIVE
HUMIDITY<80%
2.GUARANTEE PERIOD:12 MONTHS
3.OPERATION: -40°C TO +85°C
4.MANUAL SOLDERING PARAMETERS:24H
IR TEMPERATURE: 260±5°C 5~10 SECONDS.



RECOMMENDED PCB LAYOUT
PTOLERANCE=±0.05



UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS: ANGLES:		RJ45 LED SMT 8P8C 无弹带灯左黄右绿			
X	:±0.30	X	:±2°	DWN	xiong
X.X	:±0.20	X.X	:±1°	PART NO.	RJ45-884-810-3
X.XX	:±0.10	CHKD	lee	SCALE:1:1	UNIT: mm
		APVD	wang	SIZE: A4	SHEET:10F 1
					REV: A4
					CUSTOMER COPY