




A	B	C	D		E		
			REV.	DESCRIPTION	ECN NO.	NAME	DATE
1							
2							
3							
4							
5							

## NOTE

### 1. SPECIFICATIONS

WITHSTANDING VOLTAGE: 500V AC  
 CURRENT RATING: 2AMP  
 INSULATION RESISTANCE: 1000MΩ MIN  
 CONTACT RESISTANCE: 20 mΩ MAX  
 TEMPERATURE RANGE: -55°C ~ +85°C

### 2. MATERIAL

HOUSING: THERMOPLASTIC UL94V-0  
 CONTACT: BRASS

### 3. FINISH: SEE TABLE

Table:

PART NAME	Q'TY	Material
CONTACT	1	C2680R-H, NI 80U"
HOUSING	1	PBT+30%GF,BLACK
CONTACT	1	C2680R-H,GOLD FLASH
CONTACT	1	C2680R-H,GOLD 15U"
CONTACT	1	C2680R-H,GOLD 30U"
CONTACT	1	C2680R-H,半金镍0.4U"

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM. TOL. x.x ±0.30 x.xx ±0.20 x.xxx ±0.10	TITLE: 2.54mm 开口短路帽				
GENERAL ANGLE: ±1°	DWG. NO.: A254D-PT060-B				
	DRAWN: ELLA				
	UNIT: mm	SCALE: none	SHEET: 1 of 1	APPROVED: WILL	
	DWG. SIZE: A4	LAYER: bxconn			

