

Differential Probe N1008A



Characteristic

- 1% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	N1008A
Bandwidth(-3dB)	DC-50MHz
Attenuation Ratio	10X,100X
Accuracy	±1%
Rise Time	≥7ns
Input differential Vp-p	10X:80V; 100X:800V
Input differential V AC RMS	280V
Input differential V DC	10X:40V; 100X:400V
Differential mode voltage(Vpeak)	10X:40V; 100X:400V
Common mode voltage(rms)	280V
Input Impedance	2MΩ//2.5pF(Single-ended); 4MΩ//1.25pF(Both ends)
Noise RMS	10X:<10mV; 100X:<50mV
Output Voltage	<7V
Oscilloscope input impedance	1MΩ
Power adaptor	6V adapter
CMRR(Typical)	60Hz: >80dB; 100kHz: >50dB
Length of BNC Cable	90cm
Length of Input Leads	30cm
Temperature	0~50°C
Humidity	20~75%RH
Weight	284g
Dimension(L*W*H)	166.5×70.7×30mm

● ACCESSORIES



Adapter



BP-368N

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.