

AC & DC Current Probe PT710-B



Characteristic

- Overload warning function
- Two range slide switches
- The power adapter is used for power supply and the dry battery power supply device is retained
- Detachable design, sturdy and durable
- Low noise floor, more suitable for low current testing

Model	PT710-B
Bandwidth(-3dB)	DC-500KHz
Accuracy	±3%:30mA~5Apeak at 200mV/A ±4%:300mA~20Apeak at 20mV/A ±15%:20A~50Apeak at 20mV/A
Conversion Ratio	20mV/A,200mV/A
AC current	100Ap-p
AC Current RMS	35A RMS
DC current	50A DC
Measuring wire diameter	≤Φ11mm
Maximum sensitivity	5mA
Oscilloscope shows 1mV	5mA
Rise Time	0.7μs
Working Voltage	300V CAT III
Floating Voltage	600V CAT II
Temperature and Humidity	0~50°C; 20~75%RH
Weight	260g
Dimension(L×W×H)	280*70*32 mm

● ACCESSORIES



Adapter



BP-250



MT-246N

GUANGZHOU PINTECH CO.,LIMITED

Web:www.pintech.com.cn

Tel:86-20-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.