

AC & DC Current Probe PT710-C



Characteristic

- Overload warning function
- Two range slide switches
- The power adapter is used for power supply and the dry battery power supply device is retained
- Detachable design, sturdy and durable
- Low noise floor, more suitable for low current testing

Model	PT710-C
Bandwidth(-3dB)	DC-1MHz
Accuracy	±3%:20mA~14Apeak at 500mV/A ±4%:0.2A~50Apeak at 50mV/A ±15%:50A~70Apeak at 50mV/A
Conversion Ratio	50mV/A,500mV/A
AC current	140Ap-p
AC Current RMS	50A RMS
DC current	70A DC
Measuring wire diameter	≤Φ10.3mm
Maximum sensitivity	2mA
Oscilloscope shows 1mV	2mA
Rise Time	0.35μs
Working Voltage	300V CAT III
Floating Voltage	600V CAT II
Temperature and Humidity	0~50°C; 20~75%RH
Weight	260g
Dimension(L×W×H)	262*81*36 mm

● ACCESSORIES



Adapter



BP-250



MT-246N

GUANGZHOU PINTECH CO.,LIMITED

Web:www.pintech.com.cn

Tel:86-20-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.