


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.14	阿树




Voltage rating:250V AC/DC
额定电压:250V AC/DC
Current rating:1.0A
额定电流: 1.0A
Insulation resistance:1000MΩ Min
绝缘电阻: 1000MΩ Min
Withstanding voltage:≥500V AC/minute
耐压: ≥500VC/分钟
Temperature range:-40℃-+250℃
使用温度: -40℃-+250℃

PART NO.:

X1270 W V-2x25 B1-9T AuSn
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Row No-Pin No:2x25P
⑤B1:Type B Contains gaps
⑥Material:PA9T-Nylon PA9T UL94V-0
⑦Planting Category:AuSn-Plating AuSn
V01-All Gold Flash



X1270WV-2x25B1-9TV01	Nylon-9T UL 94V-0	Brass	Gold Flash	X1270H2-2xXX
X1270WV-2x25B1-9TAuSn			Plating AuSn	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 1.27mm BTB Style Connectors
CHECKED		UNIT:	mm/in	PART NO.: X1270WV-2xXXB1-9TXX
APPROVED		SIZE:	A4	DWG NO.: