






RoHS




Circuit Diagram



PCB Layout(Pattern Side)



凸柄  
Convex handle



短柄  
Short handle

NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance:≥100 MΩ
- 3.Withstand voltage:AC 500V 1Minute
- 4.Operating Force Range: 1000gf Max
- 5.Mechanical Life:3,000 Cycles

| Number of digits(位数) |                     | 1P     | 2P     | 3P     | 4P     | 5P     | 6P     | 7P     | 8P     | 9P     | 10P    | 12P    |
|----------------------|---------------------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| Cover/red<br>盖子/红色   | 凸柄<br>Convex handle | DA-01  | DA-02  | DA-03  | DA-04  | DA-05  | DA-06  | DA-07  | DA-08  | DA-09  | DA-10  | DA-12  |
|                      | 短柄<br>Short handle  | DA-01D | DA-02D | DA-03D | DA-04D | DA-05D | DA-06D | DA-07D | DA-08D | DA-09D | DA-10D | DA-12D |
| Cover/blue<br>盖子/蓝色  | 凸柄<br>Convex handle | DA-01R | DA-02R | DA-03R | DA-04R | DA-05R | DA-06R | DA-07R | DA-08R | DA-09R | DA-10R | DA-12R |
|                      | 短柄<br>Short handle  | DA-01L | DA-02L | DA-03L | DA-04L | DA-05L | DA-06L | DA-07L | DA-08L | DA-09L | DA-10L | DA-12L |

|     |              |        |     |                   |              |
|-----|--------------|--------|-----|-------------------|--------------|
| Ⓔ   | Terminal     |        | 8   | Phosphorus bronze | Gold plating |
| Ⓓ   | Potting glue |        |     | Epoxy resin       | Black        |
| Ⓒ   | Handle       |        | 4   | PBT               | White        |
| Ⓑ   | Cover        |        | 1   | PBT               | Red/Blue     |
| Ⓐ   | Base         |        | 1   | PBT               | Black        |
| NO. | Name         | Number | Qty | Materil           | Remarks      |

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

|          |      |       |            |
|----------|------|-------|------------|
| design   | date | name  | DIP SWITCH |
| Review   | date | model | DA-04      |
| Approved | date |       |            |

Drawing number: 1:1 unit mm gape number A4