








说明:

1. 产品表面清洁, 无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料: LCP UL94V-0, 颜色: 本色;
3. 焊片: 黄铜, 镀底30u"Min., 镀锡50u"Min.;
4. 接触针: 黄铜, 镀底30u"Min., 镀锡50u"Min.;
5. 满足灼热丝温度850度.
6. 工作温度: -40~+85°C
7. 额定电流: 3A AC/DC
8. 额定电压: 250V AC/DC
9. 接触阻抗: 10mΩ Max.
10. 绝缘阻抗: 1000MΩ Min.
11. 耐压: 1000V AC FOR 1 MINUTE

序号	名称	数量
1	基座	1
2	阳接触针	n
3	焊片	2



P/N	PIN	DIM A	DIM B	DIM C
XY-HA2.54-2PLT	2	2.50	9.90	5.90
XY-HA2.54-3PLT	3	5.00	12.40	8.40
XY-HA2.54-4PLT	4	7.50	14.90	10.90
XY-HA2.54-5PLT	5	10.00	17.40	13.40
XY-HA2.54-6PLT	6	12.50	19.90	15.90
XY-HA2.54-7PLT	7	15.00	22.40	18.40
XY-HA2.54-8PLT	8	17.50	24.90	20.90
XY-HA2.54-9PLT	9	20.00	27.40	23.40
XY-HA2.54-10PLT	10	22.50	29.90	25.90
XY-HA2.54-11PLT	11	25.00	32.40	28.40
XY-HA2.54-12PLT	12	27.50	34.90	30.90
XY-HA2.54-13PLT	13	30.00	37.40	33.40
XY-HA2.54-14PLT	14	32.50	39.90	35.90
XY-HA2.54-15PLT	15	35.00	42.40	38.40
XY-HA2.54-16PLT	16	37.50	44.90	40.90
XY-HA2.54-17PLT	17	40.00	47.40	43.40
XY-HA2.54-18PLT	18	42.50	49.90	45.90
XY-HA2.54-19PLT	19	45.00	52.40	48.40
XY-HA2.54-20PLT	20	47.50	54.90	50.90



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.50	X.*± 5°	APR. Alex	TITLE: HA-SMT-A带扣插座		
.XX±0.20	.X.*± 3°	CHK. Jack	DWG NO. XY-HA2.54-NPLT		
.XXX±0.10	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1