




Cable Assemblies > Data Bus Components > Data Bus Connectors



Data Bus Connector Type: **Plug**

Data Bus Connector Style: **Threaded**

Contact Type: **Pin**

Features

Product Type Features

Data Bus Connector Type	Plug
Data Bus Connector Style	Threaded

Contact Features

Contact Type	Pin
--------------	-----

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
-----------------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (.37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process CapabilityNot applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CR4852-000
D-500-0457-2-614-060



TE Part # 685041-000
D-500-0457-1-612-079



TE Part # 444404-000
D-500-L455-1-612-078



TE Part # 232371-000
D-500-0457-2-613-160




TE Part # CB0150-000
D-500-L455-1-613-078



TE Part # CR5949-000
D-500-L457-2-612-120




TE Part # CR5960-000
D-500-L457-1-612-236



TE Part # 864503-000
D-500-0456-2-612-079




TE Part # EM3477-000
D-500-L458-6-612-078




TE Part # 943333-000
D-500-0455-2-613-160



TE Part # F59780-000
D-500-L456-3-612-240



TE Part # 816300-000
D-500-0458-2-612-079



TE Part # 116273-000
[D-500-0455-2-612-120](#)




TE Part # 392641-000
[D-500-0455-1-613-240](#)



TE Part # 207547-000
[D-500-0458-1-613-012](#)



TE Part # 496550-000
[D-500-0458-1-612-240](#)




TE Part # 610565-000
[D-500-0455-2-613-240](#)



TE Part # 134865-000
[D-500-0456-2-613-079](#)



TE Part # D84971-000
[D-500-L455-1-612-120](#)



TE Part # CL3698-000
[D-500-L458-3-614-120](#)


Customers Also Bought



TE Part #A11769-000
[D-150-0321](#)




TE Part #624512-000
[D-146-0207](#)




TE Part #697039-000
[D-659-0039](#)




TE Part #981759-000
[MTCC1P-COAX-01P-01](#)



TE Part #953271-000
[D-659-0086](#)



TE Part #575569-000
[D-621-0406](#)




TE Part #699874-000
[CTA-0025](#)



TE Part #2102353-6
[CeeLok FAS-T, Plug Kit, ZnNi, B](#)



TE Part #1-2327906-4
[KEYED GUIDE PIN , MACHINED, MULTIGIG BP](#)



TE Part #6339191-5
[MJ,RJ45,SMT,SHLD,LED\(G/G\)](#)

Documents



Product Drawings

DK-621-0411-P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_902973-000_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_902973-000_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_902973-000_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Data Bus Components Brochure

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English