




说明:


1. 产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料:LCP UL94V-0,颜色:本色;
3. 焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
4. 接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
5. 满足灼热丝温度850度.
6. 工作温度-40~+85°C
7. 额定电流:2A AC/DC
8. 额定电压:100V AC/DC
9. 接触阻抗:10mΩ Max.
10. 绝缘阻抗:1000MΩ Min.
11. 耐电压:800V AC FOR 1 MINUTE



序号	名称	数量
1	基座	1
2	阳接触针	n
3	定位焊片	2



P/N	PIN	DIM A	DIM B	DIM C
XY-PH2.0-2PWT	2	2.00	7.90	4.7000
XY-PH2.0-3PWT	3	4.00	9.90	6.7000
XY-PH2.0-4PWT	4	6.00	11.90	8.7000
XY-PH2.0-5PWT	5	8.00	13.90	10.7000
XY-PH2.0-6PWT	6	10.00	15.90	12.7000
XY-PH2.0-7PWT	7	12.00	17.90	14.7000
XY-PH2.0-8PWT	8	14.00	19.90	16.7000
XY-PH2.0-9PWT	9	16.00	21.90	18.7000
XY-PH2.0-10PWT	10	18.00	23.90	20.7000
XY-PH2.0-11PWT	11	20.00	25.90	22.7000
XY-PH2.0-12PWT	12	22.00	27.90	24.7000
XY-PH2.0-13PWT	13	24.00	29.90	26.7000
XY-PH2.0-14PWT	14	26.00	31.90	28.7000
XY-PH2.0-15PWT	15	28.00	33.90	30.7000
XY-PH2.0-16PWT	16	30.00	35.90	32.7000
XY-PH2.0-17PWT	17	32.00	37.90	34.7000
XY-PH2.0-18PWT	18	34.00	39.90	36.7000
XY-PH2.0-19PWT	19	36.00	41.90	38.7000
XY-PH2.0-20PWT	20	38.00	43.90	40.7000



DIMENSION IN mm

TOLERANCE UNLESS
OTHERWISE SPECIFIED

.X±0.50

X.*±5°

.XX±0.20

.X.*±3°

.XXX±0.10

.XX.*±1°

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd

APR. Alex

TITLE:
PH-SMT-AW轴座

CHK. Jack

DWG NO. XY-PH2.0-NPWT

DRA. Can

PROJ.

CUSTOMER DRAWING

SIZE A4

SCALE 1:1

SHEET 1/1

REV. A