



The Main Thchnology Performance

Rate voltage,current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	250/180±30gf
Travel	0.20±0.10mm
Insulated resistance	≥100MΩ
Dielectric strength	≥250VAC/1min



PCB.WELDING DRAWING

CIRCUIT DIAGRAM



E	按钮	PPA	1	黑色
D	盖板	铁盖板	1	镀铜锡
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR
------	-------------	----------	-----	-------------

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 6x6 SMD TACT SWITCH	
.X±0.35	X.*± 5°	CHK.	Jack	DWG NO. XY-6X6XNH-STM	
.XX±0.25	.X.*± 3°	DRA.	Can	PROJ.  CUSTOMER DRAWING	
.XXX±0.15	.XX.*± 1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A