





SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min


Operation Temperature:-40°c to +105°c

Contact Material:Brass

Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard:PBT

Max.Processing Temp:180°C for 30-60 seconds
(200°C for 10 seconds)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.50	X.*± 5°	APR.	Alex	TITLE: 2.00 Mini Jumper 1*2Pin Close Type	
.XX±0.20	.X*± 3°	CHK.	Jack	DWG NO. XY-200D-PT-065-B	
.XXX±0.10	.XX*± 1°	DRA.	Can	PROJ. 	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1