


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	①X9	产品结构及尺寸变更，图面升级整理图面	2025.07.16	阿树



- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:3A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance: $\geq 1000M\Omega$
 - Contact resistance: $\leq 20m\Omega$
 - After environmental testing: $\leq 30m\Omega$

PART NO.:

X9556 I F-P SN
① ② ③ ④ ⑤

- ①Series Number.
②Category: T-terminal
③Shape:F-Female
④Material: B-Brass,P-Phosphorous broze
⑤Plating Category:SN-Bright Tin Plating

X9556TF-PSN	Phosphor Bronze	Tin-plated	AWG#28~#22	1.63mm(Max)	X9556H
X9556TF-BSN	Brass	Stamping Before Plating:30u" Ni;70u"Sn	AWG#22-#26		
PART NO	Material	Finish	Wire Range	Insulation O.D.	Suitable XKB Housing

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

阿树

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
2.54mm Crimp Style Connector
PART NO.:
X9556TF-PSN
DWG NO.: