








序号	名称	数量
1	基座	1
2	阳接触针	n
3	焊片	2



P/N	PIN	DIM A	DIM B	DIM C
XY-HY2.0-2PLT	2	2.00	8.00	4.80
XY-HY2.0-3PLT	3	4.00	10.00	6.80
XY-HY2.0-4PLT	4	6.00	12.00	8.80
XY-HY2.0-5PLT	5	8.00	14.00	10.80
XY-HY2.0-6PLT	6	10.00	16.00	12.80
XY-HY2.0-7PLT	7	12.00	18.00	14.80
XY-HY2.0-8PLT	8	14.00	20.00	16.80
XY-HY2.0-9PLT	9	16.00	22.00	18.80
XY-HY2.0-10PLT	10	18.00	24.00	20.80
XY-HY2.0-11PLT	11	20.00	26.00	22.80
XY-HY2.0-12PLT	12	22.00	28.00	24.80
XY-HY2.0-13PLT	13	24.00	30.00	26.80
XY-HY2.0-14PLT	14	26.00	32.00	28.80
XY-HY2.0-15PLT	15	28.00	34.00	30.80
XY-HY2.0-16PLT	16	30.00	36.00	32.80
XY-HY2.0-17PLT	17	32.00	38.00	34.80
XY-HY2.0-18PLT	18	34.00	40.00	36.80
XY-HY2.0-19PLT	19	36.00	42.00	38.80
XY-HY2.0-20PLT	20	38.00	44.00	40.80



PCB LAYOUT



说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:2A AC/DC
- 8.额定电压:100V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐电压:800V AC FOR 1 MINUTE

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: PHB-SMT-A		
.X±0.50	.X*±5°	Alex	DWG NO. XY-HY2.0-NPLT		
.XX±0.20	.X*±3°	Jack	PROJ. CUSTOMER DRAWING		
.XXX±0.10	.XX*±1°	Can	SIZE A4	SCALE 1:1	SHEET 1/1
			REV.	A	