







说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 5.满足灼热温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:3A AC/DC
- 8.额定电压:250V AC/DC
- 9.接触电阻:10mΩ Max.
- 10.绝缘电阻:1000MΩ Min.
- 11.耐电压:1000V AC FOR 1 MINUTE

PCB LAYOUT
TOL.: ±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE:		
.X±0.50	X.*± 5°	Alex	TJC3-SMT-AW		
.XX±0.20	.X*± 3°	Jack	DWG NO. XY-XH2.54-NPWT		
.XXX±0.10	.XX*± 1°	Can	CUSTOMER DRAWING		
		PROJ.	SIZE A4	SCALE 1:1	SHEET 1/1
				REV.	A