






NOTE:
Technical data:
Insulator body:PBT+15% G.F UL94-V0
Curent Rating:3 AMP
Insulator resistance:1000 Megohms min
Dielectric withstanding:AC/DC 500V.
Contact Resistance:25mΩ
Contactmaterial:Bronze.
plating:Gold or tin over nickel
Operating Temperature:-40°C to +105°C



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.50	X.*± 5°	APR. Alex	TITLE: MJ PH2.0 H:3.5		
.XX±0.20	.X*± 3°	CHK. Jack	DWG NO. XY-200D-PT-060-B		
.XXX±0.10	.XX*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1