


CIRCUIT DIAGRAM




TS-1187A-XXB

高度

力度:


B: 250G

A: 180G



The Main Thchnology Performance

Rate voltage,current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	±30gf
Travel	0.20±0.10mm
Insulated resistance	≥100MΩ
Dielectric strength	≥250VAC/1min



PCB.WELDING DRAWING

TS-1187A-XAB	高度
A	1.5
B	1.6
C	1.7
D	2.0
E	2.5
F	3.0
G	3.5
H	4.0
I	4.5
J	5.0

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X*± 5°	APR. Alex	TITLE: 4x4 SMD TACT SWITCH		
.XX±0.25	.X*± 3°	CHK. Jack	DWG NO. TS-1187A-XXB		
.XXX±0.15	.XX*± 1°	DRA. Can	PROJ.		CUSTOMER DRAWING
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A