








P/N	PIN	DIM A	DIM B	DIM C
XY-GH1.25-2PLT	2	1.25	3.85	5.75
XY-GH1.25-3PLT	3	2.50	5.10	7.00
XY-GH1.25-4PLT	4	3.75	6.35	8.25
XY-GH1.25-5PLT	5	5.00	7.60	9.50
XY-GH1.25-6PLT	6	6.25	8.85	10.75
XY-GH1.25-7PLT	7	7.50	10.10	12.00
XY-GH1.25-8PLT	8	8.75	11.35	13.25
XY-GH1.25-9PLT	9	10.00	12.60	14.50
XY-GH1.25-10PLT	10	11.25	13.85	15.75
XY-GH1.25-11PLT	11	12.50	15.10	17.00
XY-GH1.25-12PLT	12	13.75	16.35	18.25
XY-GH1.25-13PLT	13	15.00	17.60	19.50
XY-GH1.25-N14PLT	14	16.25	18.85	20.75
XY-GH1.25-15PLT	15	17.50	20.10	22.00
XY-GH1.25-16PLT	16	18.75	21.35	23.25
XY-GH1.25-17PLT	17	20.00	22.60	24.50
XY-GH1.25-18PLT	18	21.25	23.85	25.75
XY-GH1.25-19PLT	19	22.50	25.10	27.00
XY-GH1.25-20PLT	20	23.75	26.35	28.25




说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 5.满足灼热温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:1A AC/DC
- 8.额定电压:50V AC/DC
- 9.接触阻抗:20mΩ Max.
- 10.绝缘阻抗:100MΩ Min.
- 11.耐压:500V AC FOR 1 MINUTE




PCB Layout


DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE:		
.X±0.50	X.*±5°	Alex	GH-SMT-A针座		
.XX±0.20	.X°±3°	CHK. Jack	DWG NO. XY-GH1.25-NPLT		
.XXX±0.10	.XX°±1°	DRA. Can	PROJ.	CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV.	A	




2PIN




3PIN




4PIN




5PIN




6PIN




7PIN




8PIN




9PIN




10PIN




11PIN




12PIN




13PIN




14PIN



15PIN



18PIN



20PIN

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.50	X.*± 5°	APR. Alex	TITLE: GH-SMT-A针座	
.XX±0.20	.X.*± 3°	CHK. Jack	DWG NO. XY-GH1.25-NPLT	
.XXX±0.10	.XX.*± 1°	DRA. Can	PROJ.	CUSTOMER DRAWING
		SIZE A4	SCALE 1:1	SHEET 1/2
		REV. A		