


REV.	SPECIFICATION	ECN NO.	APPD.
R5		ECN140328	

Material:
Housing:Thermoplastic Polyester Glass Filled UL94V-0
Contacts:Copper Alloy
Electrical Characteristics:
Current Rating: 2 AMP.
Dielectric Withstanding Voltage: AC 1000V for 1 Minute.
Insulator Resistance: 20mΩ max. at DC 100mA.
Operating Temperature: -55°C~+105°C.
***RoHS Compliant**



2044-3XxxGxxRA
Series Triple Row No. of Pin Per Row G:Gold Plated T: Tin Plated
A:Tray Package B: Bulk Package R:Right Angle
00:G/F
10:10u"
15:15u"
30:30u"

Position Dimension	6 Thru 120
A	2.54XNo.of Position/3+0.4
B	2.54XNo.of Position/3+0.4-2.54

P.C. Board Layout
(Tolerance:±0.05)

Tolerances	Dwg. No.	2044-D0000-005	Title:		WINGTAT® 深圳市格林柏电子技术开发有限公司			
x = ±0.5	Projection	⊕ ⊞	2044 Series		P/N: 2044-3XxxGxxRA			
.x = ±0.25	Unit	mm	Scale	1:1	SHEET 1/1			
.xx = ±0.15	Drawn By	ycj	03/15'16	2.54mmX2.54mm(0.100"X0.100")		Ver. No.	R5	