






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



P/N	PIN	DIM A	DIM B	DIM C
JXT-GH1.25-2PLT	2	1.25	3.85	5.75
JXT-GH1.25-3PLT	3	2.50	5.10	7.00
JXT-GH1.25-4PLT	4	3.75	6.35	8.25
JXT-GH1.25-5PLT	5	5.00	7.60	9.50
JXT-GH1.25-6PLT	6	6.25	8.85	10.75
JXT-GH1.25-7PLT	7	7.50	10.10	12.00
JXT-GH1.25-8PLT	8	8.75	11.35	13.25
JXT-GH1.25-9PLT	9	10.00	12.60	14.50
JXT-GH1.25-10PLT	10	11.25	13.85	15.75
JXT-GH1.25-11PLT	11	12.50	15.10	17.00
JXT-GH1.25-12PLT	12	13.75	16.35	18.25
JXT-GH1.25-13PLT	13	15.00	17.60	19.50
JXT-GH1.25-14PLT	14	16.25	18.85	20.75
JXT-GH1.25-15PLT	15	17.50	20.10	22.00
JXT-GH1.25-16PLT	16	18.75	21.35	23.25
JXT-GH1.25-17PLT	17	20.00	22.60	24.50
JXT-GH1.25-18PLT	18	21.25	23.85	25.75
JXT-GH1.25-19PLT	19	22.50	25.10	27.00
JXT-GH1.25-20PLT	20	23.75	26.35	28.25



说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:1A AC/DC
- 8.额定电压:50V AC/DC
- 9.接触阻抗:20mΩ Max.
- 10.绝缘阻抗:100MΩ Min.
- 11.耐电压:500V AC FOR 1 MINUTE

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.30	X':±5°	PART NO. JXT-GH1.25-XPLT	TITLE: GH-SMT-A针座	
X.X:±0.25	X.X':±3°		MANUFACTURE DWG	
X.XX:±0.20	X.XX':±1°			
UNITS	mm	DESIGN: Ethan		
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SCALE N:A	SHEET 1/1

