









序号	名称	数量
1	基座	1
2	阳接触针	n
3	焊片	2



说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:2A AC/DC
- 8.额定电压:100V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐电压:800V AC FOR 1 MINUTE

P/N		PIN	DIM A	DIM B	DIM C
JXT-HY2.0-2PLT		2	2.00	8.00	4.80
JXT-HY2.0-3PLT		3	4.00	10.00	6.80
JXT-HY2.0-4PLT		4	6.00	12.00	8.80
JXT-HY2.0-5PLT		5	8.00	14.00	10.80
JXT-HY2.0-6PLT		6	10.00	16.00	12.80
JXT-HY2.0-7PLT		7	12.00	18.00	14.80
JXT-HY2.0-8PLT		8	14.00	20.00	16.80
JXT-HY2.0-9PLT		9	16.00	22.00	18.80
JXT-HY2.0-10PLT		10	18.00	24.00	20.80
JXT-HY2.0-11PLT		11	20.00	26.00	22.80
JXT-HY2.0-12PLT		12	22.00	28.00	24.80
JXT-HY2.0-13PLT		13	24.00	30.00	26.80
JXT-HY2.0-14PLT		14	26.00	32.00	28.80
JXT-HY2.0-15PLT		15	28.00	34.00	30.80
JXT-HY2.0-16PLT		16	30.00	36.00	32.80
JXT-HY2.0-17PLT		17	32.00	38.00	34.80
JXT-HY2.0-18PLT		18	34.00	40.00	36.80
JXT-HY2.0-19PLT		19	36.00	42.00	38.80
JXT-HY2.0-20PLT		20	38.00	44.00	40.80
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±5°	PART NO.	TITLE: PHB-SMT-A		
X.X:±0.25	X.X':±3°	JXT-HY2.0-XPLT			
X.XX:±0.20	X.XX':±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olivia			
MATERILA	— — —	APPD: Ava	 SCALE SHEET		
FINISH	— — —				