









说明:

1. 产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料:LCP UL94V-0,颜色:本色;
3. 焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
4. 接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
5. 满足灼热丝温度850度.
6. 工作温度-40~+85°C
7. 额定电流:3A AC/DC
8. 额定电压:250V AC/DC
9. 接触阻抗:10mΩ Max.
10. 绝缘阻抗:1000MΩ Min.
11. 耐压:1000V AC FOR 1 MINUTE



2PIN



P/N	PIN	DIM A	DIM B	DIM C
JXT-XH2.54-2PWT	2	2.50	9.90	5.90
JXT-XH2.54-3PWT	3	5.00	12.40	8.40
JXT-XH2.54-4PWT	4	7.50	14.90	10.90
JXT-XH2.54-5PWT	5	10.00	17.40	13.40
JXT-XH2.54-6PWT	6	12.50	19.90	15.90
JXT-XH2.54-7PWT	7	15.00	22.40	18.40
JXT-XH2.54-8PWT	8	17.50	24.90	20.90
JXT-XH2.54-9PWT	9	20.00	27.40	23.40
JXT-XH2.54-10PWT	10	22.50	29.90	25.90
JXT-XH2.54-11PWT	11	25.00	32.40	28.40
JXT-XH2.54-12PWT	12	27.50	34.90	30.90
JXT-XH2.54-13PWT	13	30.00	37.40	33.40
JXT-XH2.54-14PWT	14	32.50	39.90	35.90
JXT-XH2.54-15PWT	15	35.00	42.40	38.40
JXT-XH2.54-16PWT	16	37.50	44.90	40.90
JXT-XH2.54-17PWT	17	40.00	47.40	43.40
JXT-XH2.54-18PWT	18	42.50	49.90	45.90
JXT-XH2.54-19PWT	19	45.00	52.40	48.40
JXT-XH2.54-20PWT	20	47.50	54.90	50.90

TOLERANCE

X.:±0.30

X':±5°

X.X:±0.25

X.X':±3°

X.XX:±0.20

X.XX':±1°

UNITS

mm

MATERILA

FINISH



深圳聚兴泰电子科技有限公司

Shenzhen Juxingtai Electronic Technology Co., Ltd

PART NO.

JXT-XH2.54-XPWT

DESIGN: Ethan


CHED: Olivia

APPD: Ava

TITLE:

TJC3-SMT-AW针座

MANUFACTURE DWG



SCALE

N:A

SHEET

1/1