


| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |



NOTE:  
 Technical data:  
 Insulator body:PBT+15% G.F UL94-V0  
 Curent Rating:3 AMP  
 Insulator resistance:1000 Megohoms min  
 Dielectric withstanding:AC/DC 500V.  
 Contact Resistance:25mΩ  
 Contactmaterial:Bronze.  
 plating:Gold or tin over nickel  
 Operating Temperature:-40°C to +105°C

| TOLERANCE  |       | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                          |              |              |
|------------|-------|--------------------------------------------------------------------|--------------------------|--------------|--------------|
| .X:±0.25   | ±1'   | PART NO.<br>2.0-060-PT-B                                           | TITLE:<br>MJ PH2.0 H:3.5 |              |              |
| .XX:±0.20  |       |                                                                    |                          |              |              |
| .XXX:±0.10 |       |                                                                    |                          |              |              |
| UNITS      | mm    | DESIGN: Ethan                                                      | MANUFACTURE DWG          |              |              |
| MATERILA   | — — — | CHED: Olvia                                                        |                          |              |              |
| FINISH     | — — — | APPD: Ava                                                          |                          |              |              |
|            |       |                                                                    |                          | SCALE<br>N:A | SHEET<br>1/1 |